


# OVERVÅGNINGSSYSTEM ALCA 6



- Velegnet til industrigasser
- Plasthus med gennemsigtigt låg

Laser, Svejsning, Skæring, industriel proces

## Applikationer

ALCa signal box are designed for monitoring of pressure, weight and levels through digital display. Using suitable transmitters with an electrical output signal of 4-20 mA, the contents of compressed gas containers are monitored and the current pressure is displayed at the same time

**Designet til implementering af**  
industrigasser

**Designet til**  
Distributionssystemer for AL gas

**Undtagen**  
Oxidizing and flammable mixtures are excluded

## Specifikationer

Supply voltage: ..... 230VAC +/-10%  
Measuring signal: ..... 4-20 mA (precision:  
0.5% PE)  
Sensor supply: ..... 24 VDC (20.1 mA  
max.)

Beskyttelsesklasse IP 65., Arbejdstemperatur: 0 ° C til + 50 ° C.

## INFO +

- Easy to program - Plug in play ready to use - 1.5m power supply cable included - Sticker set to identify used molecules

## Sikkerhedsalarm

⚠ Advarsel!!!! Må ikke anvendes i Ex-områder!

## Højdepunkter

- Continuous indication of the level.
- The Hardware unit have a internal alarm signal for identification of the amount of gas but also the ability to connect an external alarm unit for greater supervision.

# Dimensioner

Længde (L) : 310 mm

Højde (H) : 252 mm


Dybde (D) : 148 mm


Nettovægt : 1.6 kg

## Produkter

Model	Varenummer	Kort beskrivelse	Material
215024	ALCa 6 channel	Inerta gasser, O2	ABS / Polycarbonat
216890	ALCa 6 channel + warning light	Inerta gasser, O2	

## Options

	Model	Long designation
	16407	FITTING ELBOW G1/4 BSPP F- Ø16X1,336M

	Model	Long designation
	169933	Pressure Transmitter 400 bar_4#20mA - Inlet M12 - Outlet G1/4

## Spare parts

Model	SP Number	Long designation
215024	215235	Housing box ALCa 6 channel
216890	215235	Housing box ALCa 6 channel